






# DNH

## CAREEX-36(T)


Morrison's Public Address  
Phone: 0407442822  
Email: sales@morrisonssav.com.au

ISO 9001 CERTIFIED



100V line Primary nominal tapings	
1 : 2	6,0 W
2 : 3	3,0 W
3 : 4	1,5 W
1 : 3	1,0 W
2 : 4	0,6 W
1 : 4	0,4 W

Certified by/ Certification code / Number : NEMKO / EEx de IIB+H2 T6 Gb / Nemko10ATEX1058X  
IECEx NEM 11.0031X



Specifications	
Material / Color	Aluminum / anodized
Mounting	Foot Bracket
Termination	e-chamber, screw terminals
Weight w/transformer	2,1 kg
IP-rating	67
Max. / min. amb. temp	40°C / -20°C
Rated / max. power	6 W / 6 W
SPL 1W/1m	84 dB
SPL rated power	91 dB
Effective freq. range	180 – 15000 Hz
Dispersion (-6dB) 1kHz / 4kHz	NA
Directivity factor, Q	NA
Options	Impedances, colors, labels

### Installation, Operation and Maintenance Procedures

- Fasten loudspeaker to wall or ceiling with 4 screws by use of the extruded aluminum brackets on each side.
- Enter the e-chamber by loosening the screws on the lid and terminate the cable in the screw terminal.
- Fasten lid screws with a torque of 2 - 3 Nm to assure the IP rating.
- Use only certified/specified cable glands and blanking plugs.
- Ex-loudspeakers must be earthed correctly using the specially marked screws.
- For optimum performance, always use the correct voltage / power and operate within the frequency limits as stated.
- Do not open loudspeaker when energized.
- This loudspeaker is supplied with a 2 year warranty against defective workmanship.

DNH reserves the right to alter specifications without notice

