

the simplest solution to assistive listening



Humanteknik LA 90 Sound Shuttle. The new solution for counters and service desks.

The portable and powerful inductive loop system.

The LA-90 is a compact and portable loop system that empowers people with hearing disabilities to clearly hear what's happening around them. LA-90 transmits verbal communication directly to hearing aids as well as inductive loop receivers such as the Humanteknik LPU-1. LA-90 has been designed for spot applications in smaller proximities such as service desks and counters. Virtually installation free, simply plug LA-90 into a power source and its ready to use. In addition, LA-90 (with an in-built charging system), will run for up to four hours using its own internal power.

LA-90 captures sound via its integrated microphone and can also operate in conjunction with a second microphone by utilising the included additional mic input.


Acoustic information is automatically transformed into inductive signals then transmitted to the included inductive loop. Hearing aids equipped with a T-Coil are able to pick up these induction signals. A headphone output has also been included for added convenience and monitoring.

The discreet silver/grey chassis has been designed to be aesthetically pleasing and three colour inserts are included to ensure LA-90 blends into any environment.

LA-90 is perfect for service counters, reception desks, and any localised environment where assistive listening is required.

Technical Data

Power	
Power supply:	16V DC power pack with 1.8m cable (included)
Mains connection:	230 - 240 V AC, 50Hz
Induction Loop Output	
Range:	2m ²
Output power:	2 x 5W (10W max)
Outputs / Inputs	
Microphone Sensitivity:	60dB
Microphone input:	yes
Headphone input:	yes
Enclosure	
Dimensions (H x W x D):	200 x 185 x 70 mm
Colour:	Silver/grey (with three colour inserts: yellow, red and blue)



Morrison's Public Address
Web: www.morrisonsav.com.au
Email: sales@morrisonsav.com.au
Phone: 0407442822